



Premium SPRAY & GEL vaccination



Scan the code
FOR THE FULL
digital brochure



Ideal for NON-AUTOMATED HATCHERIES

SEMI-AUTOMATIC, no operator impact during operation

DATA COLLECTION in real time



CEVA.COM

Premium
SPRAY & GEL
vaccination

Hatchery equipment



High Spray Quality Without Automation

Flat nozzle system ensuring high level of spray **homogeneity**.

Consistent coverage from start to finish of the crate.

Automatic Gel Arm System

Gel droplet technology is the **most efficient** route of administration for Immucox range.

A **motorized arm**, combined with an **electronic dispensing syringe**, ensures a homogenous & high-quality gel droplet distribution.

Non Operator Dependent Vaccination

All critical parameters are monitored, **alerting the operator** if any part of the vaccination process deviates from the correct sequence.

The Smart Hatch Spray & Gel **user friendly design** allow any operator to start it within seconds.

Technical Description

Applications :	Day old chicks	DB :	<80Db
Vaccination Route :	Spray and Gel vaccination	Overall Dimensions :	1450x800x1500 mm
Volume :	Spray 10 ml to 20ml Gel 15 ml to 27 ml	Weight :	100 kg
Voltage supply :	100 - 240 VAC	Speed :	Up to 450 crates/hour
		Type of environment :	Indoor use only in wet location



As part of the Ceva Hatchery Immunisation Control Keys program (C.H.I.C.K), our Ceva Hatchery Specialist will monitor the good operation of the equipment and the quality of vaccination during the routine visit.